



Accessories

Sizes of Permanent Beacons



- Safe CAGE CLAMP® technology
- BA15d socket integrated in the base
- Optimum illumination
- Tube mounting
- Single hole mounting possible with cable gland



TECHNICAL SPECIFICATIONS:

Dimensions (Ø x Height):	57 mm x 87 mm
Housing:	PA-GF, high impact
Lens:	PC, transparent
	Ring: PC
Connection:	CAGE CLAMP® technology max. 2.5 mm²
Cable entry:	Cable diameter max. 11 mm
Fixing:	Tube mounting M25 x 1.5 mm
Operating voltage:	Max. 250 V
Bulb socket:	BA15d, 7 Watt max.
Bulb change:	Via removal of lens
Bulb not included in assembly.	



ORDER SPECIFICATIONS:

Voltage	12-240 V
red	209 100 00
green	209 200 00
yellow	209 300 00
clear	209 400 00
blue	209 500 00



ACCESSORIES:

Base with integrated tube, M25 x 1.5 mm					
					975 209 01
Cable gland M25 x 1.5 mm					
					975 209 02
Bulb BA15d, 5 W total length 42 mm					
Voltage	12 V	24 V	30 V	115 V	230 V
	955 840 34	955 840 35	955 840 32	955 840 57	955 840 38
LED bulb BA15d total length 42 mm					
Voltage	24 V AC/DC		115 V AC		230 V AC
Current consumption	< 45 mA		< 15 mA		< 15 mA
red	956 100 75		956 100 67		956 100 68
green	956 200 75		956 200 67		956 200 68
yellow	956 300 75		956 300 67		956 300 68
white	956 400 75		956 400 67		956 400 68
blue	956 500 75		956 500 67		956 500 68



TECHNICAL DIAGRAMS:

see page 299

See note
on page 347