

Sounder-Beacon Units

CHIASSO 100 RAZOR

How you benefit:

- | High sound level
- | Low current consumption
- | Exclusive design
- | 39 tones user-selectable
- | Automatic synchronisation
- | Second tone for 2-stage alarms
- | Volume control
- | Flexible capabilities
- | LED technology
- | Controlled separately
- | Expandable to 230 V



SPECIFICATIONS

Model	CHIASSO 100 RAZOR
Current consumption	9 – 35 mA / 4 – 6 mA
Construction	ABS FR
Operating Voltage	9 – 28 V DC
IP rating	IP54 (Shallow Base) / IP65 (Deep Base)
Alarm tones	39
Operating temperature	-20 °C to +70 °C
Body colour	red or white
Lens colour	red, amber, green, blue
Construction lens	PC

Zeichnung

