

ASKARI

How you benefit:

- | High sound output
- | Low current consumption
- | 32 tones user-selectable
- | Automatic synchronisation
- | Volume control
- | Second tone for
- | 2-stage alarms
- | VdS approval for ASKARI COMPACT



SPECIFICATIONS

Model	ASKARI COMPACT	ASKARI FLANGE	ASKARI PANEL
Current consumption	8 – 35 mA / 16 mA @ DIN-Tone	6 – 35 mA / 16 mA @ DIN-Tone	5 – 35 mA / 16 mA @ DIN-Tone
Construction	ABS	ABS	ABS
Operating Voltage	9 – 28 V DC	9 – 28 V DC	9 – 28 V DC
IP rating	IP21C (Back Box)	IP65	IP65
Approvals	VdS (G206025), CPD, CNPP		
Alarm tones	32	32	32
Operating temperature	-10 °C to +55 °C	-25 °C to +70 °C	-25 °C to +70 °C
Body colour	red or white	red or white	red or white

Zeichnung

