

SQUASHNI

How you benefit:

- | Low current consumption
- | Cover for use as single sounder
- | Low installation costs
- | Mounting platform for detector
- | VdS approval



SPECIFICATIONS

Model	SQUASHNI
Current consumption	8 – 35 mA / 16 mA @ DIN-Tone
Construction	ABS
Operating Voltage	9 – 28 V DC
IP rating	IP21C
Approvals	VdS (G206022), CPD, CNPP, UL
Alarm tones	32
Operating temperature	-10 °C to +55 °C
Body colour	red or white

Zeichnung

