



### Features:

- Universal / Full Range Input
- Interchangeable AC Heads
- Level 6 Efficiency
- Cost Effective & Highly Reliable
- 1 Year Warranty



Characteristics				
Part Number	T5785ST	T5786ST	T5787ST	T5788ST
Output Voltage	5Vdc	9Vdc	12Vdc	24Vdc
Output Current Max	3A	2.66A	2A	1A
Output Current Min	0A	0A	0A	0A
Power (Watts)	24W	24W	24W	24W
Line Regulation	+/-2%			
Hold Up Time	10mS Min.			
Ripple & Noise (mV p-p)	200mV p-p	200mV p-p	200mV p-p	200mV p-p
Protections	Input Protection Output Protection Short Circuit Protection			
Rated Input Voltage	100 - 240Vac			
Full Input Voltage Range	90 - 264Vac			
Rated Frequency	47 - 63Hz			
Efficiency	81.4%	86.2%		
Input Current (RMS Max)	0.8A Max			
Inrush Current	60A Max			
Input Power (no load)	0W			
AC Inlet	UK, Euro, US & AUS Interchangeable Plugtops			
DC Cord	1.8m Output Cable			
DC Plug	2.1mm C+ve			
Hi-Pot Speciation	Primary to Secondary: AC 3000 Vrms, 4mA, 1 minute for type test.			
Insulation Resistance	Primary to Secondary: 50 OHM to 500Vdc			
Operating Temperature	0 - 40C			
Storage Temperature	-20 to 70C			
Operating Humidity	10 - 95%			
Storage Humidity	10 - 95%			
Safety Approvals	CE, FCC, C-Tick, UL, TUV, TUV GS,			
PB-Free	Yes RoHS Compliant			
Dimensions (mm)	79.1 x 46.2 x 37.1			
Weight (Grams)	250g			