

Rapid Part Number: **56-9998** Europa Part Number: **BA9LED6F** Specifications and dimensions

- Bayonet fix LED lamp
- Low maintenance due to long lfe and high reliability
- Last 500 times as long as incandescent lamps



pliant

Features	
Colour	Blue
Voltage	110V AC/DC
Other colours available	Red, Green, White, Amber
Other voltages available	24V AC/DC, 230V AC/DC
Diameter	10mm
Overall length	23mm
Number of chips	2
Wavelength green (gallium phosphide)	5600Å
Wavelength yellow (gallium arsenide phosphide)	5800Å
Wavelength amber (gallium arsenide phosphide)	6300Å
Wavelength red (gallium arsenide phosphide)	6600Å
Degree of protection	IP55
Operating temperature	-25°C to +55°C
Life expectancy	30000 hours

() ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. All products must be installed according to manufacturers instructions.

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com website: http://www.europacomponents.com