

UNILITE

PS-IL6R

PROSAFE USB RECHARGEABLE INSPECTION LIGHT



- » 600 Lumen 5W white Samsung SMD LEDs
- » DC-USB charging cable (included)
- » Additional 100 Lumen torch in head
- » Ultra strength polycarbonate housing
- » Integral hanging hook & magnet for hands-free use
- » Multi positional hook/foldable kick stand
- » Impact resistant to 1M
- » Rear charging point with protective cover

4½-24
HOURS
RUNTIME

60
METRE
BEAM RANGE

600
LUMENS
OUTPUT

IP54
DUST & WATER
RESISTANCE

BATTERY 3.7v 4400 mAh Li-ion rechargeable battery (Inc.)
WEIGHT 260g (with battery)
DIMENSION 205 x 60 x 42mm



DC-USB CABLE (INC)



USEFUL MAGNET AND HOOK



SMOOTH EVEN LIGHT SPREAD



100 LUMEN TORCH HEAD

