



### Set 5 pcs



Code		
<b>B219.025</b>	1	360
B194 T10x75; T15x100; T20x100; T25x125; T30x150		

### Set 6 pcs



Code		
<b>B219.026</b>	1	450
B191 0,5x3,0x75; 0,8x 4,0x100		
B192 PH1x100; PH2x125		
B193 PZ1x100; PZ2x125		

### Set 5 pcs



Code		
<b>B219.035</b>	1	355
B141 TR10x75; TR15x100; TR20x100; TR25x125; TR30x150		

### Set 7 pcs



Code		
<b>B219.007</b>	1	530
B193 PZ1x100; PZ2x125		
B194 T10x75; T15x100; T20x100; T25x125; T30x150		

### Set 6 pcs



Code		
<b>B219.006</b>	1	450
B191 0,5x3,0x75; 0,8x4,0x100		
B190 1,0x5,5x125; 1,2x6,5x125		
B192 PH1x100; PH2x125		

### Set 7 pcs



Code		
<b>B219.017</b>	1	530
B191 0,6x3,5x100; 0,8x 4,0x100		
B190 1,0x5,5x125; 1,2x6,5x125; 1,6x8,0x150		
B192 PH1x100; PH2x125		

### Set 6 pcs



Code		
<b>B219.016</b>	1	450
B191 0,5x3,0x75; 0,8x4,0x100		
B190 1,0x5,5x125; 1,2x6,5x125		
B193 PZ1x100; PZ2x125		

