

5mm Side Header Closed 15A Terminal Blocks

Specifications

Pitch: 5.0mm

Type: Horizontal, Closed-ended

Poles: 2 to 12 Rated Voltage: 300V Rated Current: 15A

Operational Temperature: -40° C to $+105^{\circ}$ C Withstand Voltage: 2500V AC for 60s Insulation Resistance: $500M\Omega$ at 500V DC

Wave Soldering: 260°C for 5s Hand Soldering: 350°C for 10s

Colour and Materials

Housing Colour: Green
Housing Material: PA66
Flame Retardancy: UL94-V0


Pin Header: Tin-plated brass









Order Code	Poles	Order Code	Poles
21-2824	2	21-2829	8
21-2825	3	21-2925	9
21-2826	4	21-2830	10
21-2827	5	21-2926	11
21-2828	6	21-2831	12
21- 2924	7		







Measurements are in mm unless stated otherwise.

For further information on pricing, delivery, and long-term stock agreements please get in touch with your local business development contact. Telephone our main office on **01206 751166** or email **Sales@Rapidonline.com**.



The information contained in this datasheet is subject to change without notice and replaces all data sheets previously supplied.

564513_v2.0 Page 1 of 1