

5.08mm Female Pluggable Horizontal 15A Terminal Blocks

Specifications

Pitch: 5.08mm
Type: Pluggable
Poles: 2 to 12
Rated Voltage: 300V
Rated Current: 15A


 $\begin{array}{lll} \mbox{Operational Temperature:} & -40\mbox{°C to } +105\mbox{°C} \\ \mbox{Withstand Voltage:} & 2500\mbox{V AC for } 60\mbox{s} \\ \mbox{Insulation Resistance:} & 500\mbox{M}\Omega \mbox{ at } 500\mbox{V DC} \\ \mbox{Wire Range:} & 26-12\mbox{AWG, } 2.5\mbox{mm}^2 \end{array}$


Wire Stripping Length: 6-7mm ± 0.5mm
Screw Size: M2.5
Max. Torque Value: 0.4Nm
Wave Soldering: 260°C for 5s
Hand Soldering: 350°C for 10s

Colour and Materials

Housing Colour: Green
Housing Material: PA66
Flame Retardancy: UL94-V0


Screw: Zinc-plated steel (A3)
Wire Cage: Nickel-plated brass
Contact: Phosphor bronze







Order Code	Poles	Order Code	Poles
21-2840	2	21-2845	8
21-2841	3	21-2938	9
21-2842	4	21-2846	10
21-2843	5	21-2939	11
21-2844	6	21-2847	12
21-2880	7		



Measurements are in mm unless stated otherwise.

For further information on pricing, delivery, and long-term stock agreements please get in touch with your local business development contact. Telephone our main office on **01206 838000** or email **Sales@Rapidonline.com**.



The information contained in this datasheet is subject to change without notice and replaces all data sheets previously supplied.

564515_V2.0 Page 1 of 1