

Specifications

Pitch: Type: Poles: Rated Voltage: Rated Current: Operational Temperature: Withstand Voltage: Insulation Resistance: Wave Soldering: Hand Soldering: 5.08mm Horizontal, Closed-ended 2 to 12 See Table See Table -40° C to $+105^{\circ}$ C 2500V AC for 60s 500M Ω at 500V DC 260^{\circ}C for 5s 350^{\circ}C for 10s

Colour and Materials


Housing Colour: Housing Material: Flame Retardancy: Pin Header: Green PA66 UL94-V0 Tin-plated brass


5.08mm Header Side Entry Closed 15A Terminal Blocks




Order Code	Poles	Order Code	Poles
21-2864	2	21-2869	8
21-2865	3	21-2952	9
21-2866	4	21-2870	10
21-2867	5	21-2953	11
21-2868	6	21-2871	12
21-2951	7		

Standard	Rated Voltage	Rated Current
UL	300V	15A
IEC	320V	20A





Measurements are in mm unless stated otherwise.





The information contained in this datasheet is subject to change without notice and replaces all data sheets previously supplied.