


50W AC-DC Interchangeable Power Supplies

- FR4 PCB
- 100% ATE Tested
- High Reliability
- Built in OVP, OCP & SCP
- 100% smart burn-in test for 4 hours
- Level VI Efficiency Regulations Compliant
- Universal Input 90~260V AC 47~63Hz



DIMENSIONS



15DYS650

SPECIFICATIONS

Input	Input Range	100~240VAC (Full Range), 50/60Hz
	Input Current (RMS)	1.3A@90VAC 0.6A@264VAC
Output	Voltage Range	9~30VDC
	Voltage Regulation	+/- 5% At Constant Voltage Mode
	Current Range	0.1~5A
	Max Power	50W
Energy Saving		NRCAN, DOE, ERP, GEMS, Efficiency Level VI
Environmental Protection		RoHS, REACH, PAHS
Environmental	Operating Temperature	0°C ~45°C Ambient
	Storage Temperature	-20°C ~+80°C
	Operating Humidity	10~90% (Non-condensing)
	Relative Humidity	5~95% (Non-condensing)
	MTBF	>25,000 hours at 80% load and 25°C ambient temperature
Approvals		Certified to several international approvals to EN 60950-1 & EN 60065

VAT No. GB 771 1607 40

Registered in England No. 4063412

Weee Reg. WEE/DD0749YY



+44 (0) 845 260 3400



enquiries@ideалpower.co.uk



ideалpower.co.uk

Ideal Power Ltd.
 14 Larks Way
 Tree Beech Enterprise Park
 Gunn, Barnstaple
 Devon, EX32 7NZ
 England, UK