



WorkBrite 800 | 1500 | 2500 | 4000

Key features:

- 4 Models 800-4000 Lumens
- Slim fold flat design
- Supplied with heavy duty HO5RN-F cable
- ABS Robust robust housing
- Built-in fold flat design & carry handle design
- Tempered glass
- Anti glare operation
- Supplied with:
5 metre HO5RN-F 3G x 1.00mm cable and plug

Optional Accessories:

- Optional tripod available



220-240V



IP65



1 Metre
Impact
Resistance



PRODUCT CODE	LUMENS	FLOOD BEAM	DIMENSIONS	WEIGHT
NSWORKBRITE800	800	10 Metre	(L)192x(W)171x(D)52mm	0.83KG
NSWORKBRITE1500	1500	15 Metre	(L)220x(W)194x(D)52mm	1.09KG
NSWORKBRITE2500	2500	25 Metre	(L)255x(W)285x(D)63mm	1.66KG
NSWORKBRITE4000	4000	30 Metre	(L)335x(W)302x(D)63mm	2.16KG