



Type	32/0.2
Description	Stranded Def Stan 61-12 Part 6 Cable
Conductor	Tinned Copper
Insulation	PVC
Insulation Thickness	0.34mm
Insulation Diameter	1.05mm Nominal
Conductor Resistance	238Ω/m at 20 ⁰ C (nominal)
Colours	Black, Red, Blue, Brown, Green, Grey, Orange, Pink, Violet, White, Yellow
Max Working Voltage	1500V
Cable Weight	8.5kg reel weight (nominal)
Temperature Rating	+85 ⁰ C
Length Supplied	100m + 500m
Applicable Standards	Def Stan 61-12 Part 6

* Figure is nominal, exact number of strands used may be lower