

QUICK DRYING TUNG OIL LIBERON - 526

SAFETY DATA SHEET

(REACH regulation (EC) n° 1907/2006 - n° 453/2010)

SECTION 1 : IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name : QUICK DRYING TUNG OIL LIBERON

Product code : 526.

1.2. Relevant identified uses of the substance or mixture and uses advised against

Oil

1.3. Details of the supplier of the safety data sheet

Registered company name : LIBERON Ltd.

Address : Mountfield Industrial Estate.NEW ROMNEY.KENT TN28 8XU.ENGLAND.

Telephone : (+44) 1797 36 75 55. Fax : (+44) 1797 36 75 75.

fds.produits@v33.com

www.liberon.co.uk

1.4. Emergency telephone number : .

Association/Organisation : .

Other emergency numbers

UK - National Poisons Information Service

SECTION 2 : HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

In compliance with EC regulation No. 1272/2008 and its amendments.

Flammable liquid, Category 3 (Flam. Liq. 3, H226).

May produce an allergic reaction (EUH208).

This mixture does not present a health hazard with the exception of possible occupational exposure thresholds (see paragraphs 3 and 8).

This mixture does not present an environmental hazard. No known or foreseeable environmental damage under standard conditions of use.

In compliance with directives 67/548/EEC, 1999/45/EC and their amendments.

Flammable (R 10).

May produce an allergic reaction.

Vapours may cause drowsiness and dizziness (R 67).

This mixture does not present an environmental hazard. No known or foreseeable environmental damage under standard conditions of use.

2.2. Label elements

In compliance with EC regulation No. 1272/2008 and its amendments.

Hazard pictograms :



GHS02

Signal Word :

WARNING

Additional labeling :

EUH208 Contains 2-BUTANONE OXIME. May produce an allergic reaction.

Hazard statements :

H226 Flammable liquid and vapour.

Precautionary statements - General :

P102 Keep out of reach of children.

Precautionary statements - Prevention :

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P271 Use only outdoors or in a well-ventilated area.

Precautionary statements - Disposal :

P501 Dispose of contents/container to a waste collection center (contact the local authority)

QUICK DRYING TUNG OIL LIBERON - 526**2.3. Other hazards**

The mixture does not contain any substances classified as 'Substances of Very High Concern' (SVHC) by the European Chemicals Agency (ECHA) under article 57 of REACH: <http://echa.europa.eu/fr/candidate-list-table>

The mixture satisfies neither the PBT nor the vPvB criteria for mixtures in accordance with annexe XIII of the REACH regulations EC 1907/2006.

SECTION 3 : COMPOSITION/INFORMATION ON INGREDIENTS**3.1. Substances**

No substances fulfil the criteria set forth in annexe II section A of the REACH regulation (EC) n° 1907/2006.

3.2. Mixtures**Composition :**

Identification	(EC) 1272/2008	67/548/EEC	Note	%
INDEX: Z470 EC: 919-857-5 REACH: 01-2119463258-33 HYDROCARBONS, C9-C11, N-ALKANES, ISOALKANES, CYCLICS, <2% AROMATICS	GHS07, GHS08, GHS02 Dgr Flam. Liq. 3, H226 Asp. Tox. 1, H304 STOT SE 3, H336 EUH:066	Xn Xn;R65 R10 R66-R67		10 <= x % < 25
INDEX: Z126 CAS: 57-55-6 EC: 200-338-0 REACH: 01-2119456809-23 1,2-PROPANEDIOL			[1]	0 <= x % < 2.5
INDEX: 616-014-00-0 CAS: 96-29-7 EC: 202-496-6 REACH: 01-2119539477-28 2-BUTANONE OXIME	GHS08, GHS05, GHS07 Dgr Carc. 2, H351 Acute Tox. 4, H312 Eye Dam. 1, H318 Skin Sens. 1, H317	Xn Carc. Cat. 3;R40 Xn;R21 Xi;R41-R43	[2]	0 <= x % < 2.5

Information on ingredients :

[1] Substance for which maximum workplace exposure limits are available.

[2] Carcinogenic, mutagenic or reprotoxic (CMR) substance.

SECTION 4 : FIRST AID MEASURES

As a general rule, in case of doubt or if symptoms persist, always call a doctor.

NEVER induce swallowing by an unconscious person.

4.1. Description of first aid measures**In the event of exposure by inhalation :**

In the event of an allergic reaction, seek medical attention.

In the event of splashes or contact with eyes :

Wash thoroughly with soft, clean water for 15 minutes holding the eyelids open.

In the event of splashes or contact with skin :

In the event of an allergic reaction, seek medical attention.

In the event of swallowing :

In the event of swallowing, if the quantity is small (no more than one mouthful), rinse the mouth with water and consult a doctor.

Keep the person exposed at rest. Do not force vomiting.

Seek medical attention, showing the label.

If swallowed accidentally, call a doctor to ascertain whether observation and hospital care will be necessary. Show the label.

4.2. Most important symptoms and effects, both acute and delayed

No data available.

4.3. Indication of any immediate medical attention and special treatment needed

No data available.

QUICK DRYING TUNG OIL LIBERON - 526

SECTION 5 : FIREFIGHTING MEASURES

Flammable.

Chemical powders, carbon dioxide and other extinguishing gas are suitable for small fires.

5.1. Extinguishing media

Keep packages near the fire cool, to prevent pressurised containers from bursting.

Suitable methods of extinction

In the event of a fire, use :

- sprayed water or water mist
- water with AFFF (Aqueous Film Forming Foam) additive
- halon
- foam
- multipurpose ABC powder
- BC powder
- carbon dioxide (CO₂)

Prevent the effluent of fire-fighting measures from entering drains or waterways.

Unsuitable methods of extinction

In the event of a fire, do not use :

- water jet

5.2. Special hazards arising from the substance or mixture

A fire will often produce a thick black smoke. Exposure to decomposition products may be hazardous to health.

Do not breathe in smoke.

In the event of a fire, the following may be formed :

- carbon monoxide (CO)
- carbon dioxide (CO₂)

5.3. Advice for firefighters

Fire-fighting personnel are to be equipped with autonomous insulating breathing apparatus.

SECTION 6 : ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Consult the safety measures listed under headings 7 and 8.

For non fire-fighters

Because of the organic solvents contained in the mixture, eliminate sources of ignition and ventilate the area.

For fire-fighters

Fire-fighters will be equipped with suitable personal protective equipment (See section 8).

6.2. Environmental precautions

Contain and control the leaks or spills with non-combustible absorbent materials such as sand, earth, vermiculite, diatomaceous earth in drums for waste disposal.

Prevent any material from entering drains or waterways.

6.3. Methods and material for containment and cleaning up

Clean preferably with a detergent, do not use solvents.

6.4. Reference to other sections

No data available.

SECTION 7 : HANDLING AND STORAGE

Requirements relating to storage premises apply to all facilities where the mixture is handled.

7.1. Precautions for safe handling

Always wash hands after handling.

Ensure that there is adequate ventilation, especially in confined areas.

Fire prevention :

Handle in well-ventilated areas.

Vapours are heavier than air. They can spread along the ground and form mixtures that are explosive with air.

Prevent the formation of flammable or explosive concentrations in air and avoid vapor concentrations higher than the occupational exposure limits.

Prevent the accumulation of electrostatic charges with connections to earth.

QUICK DRYING TUNG OIL LIBERON - 526

The mixture can become electrostatically charged : always earth during decanting operations. Wear antistatic shoes and clothing and floors should be electrically conductive.

Use the mixture in premises free of naked flames or other sources of ignition and ensure that electrical equipment is suitably protected.

Keep packages tightly closed and away from sources of heat, sparks and naked flames.

Do not use tools which may produce sparks. Do not smoke.

Prevent access by unauthorised personnel.

Recommended equipment and procedures :

For personal protection, see section 8.

Observe precautions stated on label and also industrial safety regulations.

Packages which have been opened must be reclosed carefully and stored in an upright position.

Prohibited equipment and procedures :

No smoking, eating or drinking in areas where the mixture is used.

7.2. Conditions for safe storage, including any incompatibilities

No data available.

Storage

Keep out of reach of children.

Keep the container tightly closed in a dry, well-ventilated place.

Keep away from all sources of ignition - do not smoke.

Keep well away from all sources of ignition, heat and direct sunlight.

Avoid accumulation of electrostatic charges.

The floor must be impermeable and form a collecting basin so that, in the event of an accidental spillage, the liquid cannot spread beyond this area.

Packaging

Always keep in packaging made of an identical material to the original.

7.3. Specific end use(s)

No data available.

SECTION 8 : EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

No data available.

Occupational exposure limits :

- UK / WEL (Workplace exposure limits, EH40/2005, 2007) :

CAS	TWA :	STEL :	Ceiling :	Definition :	Criteria :
57-55-6	150 ppm	-	-	-	-

8.2. Exposure controls

Personal protection measures, such as personal protective equipment

Use personal protective equipment that is clean and has been properly maintained.

Store personal protective equipment in a clean place, away from the work area.

Never eat, drink or smoke during use. Remove and wash contaminated clothing before re-using. Ensure that there is adequate ventilation, especially in confined areas.

- Eye / face protection

Avoid contact with eyes.

Use eye protectors designed to protect against liquid splashes

Before handling, wear safety goggles in accordance with standard EN166.

- Hand protection

Wear suitable protective gloves in the event of prolonged or repeated skin contact.

Type of gloves recommended :

- Nitrile rubber (butadiene-acrylonitrile copolymer rubber (NBR))

- PVA (Polyvinyl alcohol)

- Body protection

Work clothing worn by personnel shall be laundered regularly.

After contact with the product, all parts of the body that have been soiled must be washed.

QUICK DRYING TUNG OIL LIBERON - 526

SECTION 9 : PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

General information :

Physical state : Viscous liquid.

Important health, safety and environmental information

pH : Not relevant.
Boiling point/boiling range : Not relevant.
Flash Point Interval : 23°C <= PE <= 55°C
Vapour pressure (50°C) : Not relevant.
Density : 0.85-0.95
Water solubility : Insoluble.
Melting point/melting range : Not relevant.
Self-ignition temperature : Not relevant.
Decomposition point/decomposition range : Not relevant.

9.2. Other information

No data available.

SECTION 10 : STABILITY AND REACTIVITY

10.1. Reactivity

No data available.

10.2. Chemical stability

This mixture is stable under the recommended handling and storage conditions in section 7.

10.3. Possibility of hazardous reactions

When exposed to high temperatures, the mixture can release hazardous decomposition products, such as carbon monoxide and dioxide, fumes and nitrogen oxide.

10.4. Conditions to avoid

Any apparatus likely to produce a flame or to have a metallic surface at high temperature (burners, electric arcs, furnaces etc.) must not be allowed on the premises.

Avoid :

- accumulation of electrostatic charges.
- heating
- heat
- flames and hot surfaces

10.5. Incompatible materials

10.6. Hazardous decomposition products

The thermal decomposition may release/form :

- carbon monoxide (CO)
 - carbon dioxide (CO₂)
-

SECTION 11 : TOXICOLOGICAL INFORMATION

11.1. Information on toxicological effects

Splashes in the eyes may cause irritation and reversible damage

11.1.1. Substances

No toxicological data available for the substances.

11.1.2. Mixture

Respiratory or skin sensitisation :

Contains at least one sensitising substance. May cause an allergic reaction.

SECTION 12 : ECOLOGICAL INFORMATION

12.1. Toxicity

12.1.2. Mixtures

No aquatic toxicity data available for the mixture.

12.2. Persistence and degradability

No data available.

QUICK DRYING TUNG OIL LIBERON - 526**12.3. Bioaccumulative potential**

No data available.

12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

No data available.

12.6. Other adverse effects

No data available.

SECTION 13 : DISPOSAL CONSIDERATIONS

Proper waste management of the mixture and/or its container must be determined in accordance with Directive 2008/98/EC.

CAUTION: Oil cloths can self combust. Do not leave impregnated cloths in bundles. Before discarding lay them flat outside to dry to avoid a fire hazard.

13.1. Waste treatment methods

Do not pour into drains or waterways.

Waste :

Waste management is carried out without endangering human health, without harming the environment and, in particular without risk to water, air, soil, plants or animals.

Recycle or dispose of waste in compliance with current legislation, preferably via a certified collector or company.

Do not contaminate the ground or water with waste, do not dispose of waste into the environment.

Soiled packaging :

Empty container completely. Keep label(s) on container.

Give to a certified disposal contractor.

SECTION 14 : TRANSPORT INFORMATION

Transport product in compliance with provisions of the ADR for road, RID for rail, IMDG for sea and ICAO/IATA for air transport (ADR 2013 - IMDG 2012 - ICAO/IATA 2013).

14.1. UN number

1263

14.2. UN proper shipping name

UN1263=PAINT (including paint, lacquer, enamel, stain, shellac, varnish, polish, liquid filler and liquid lacquer base) or PAINT RELATED MATERIAL (including paint thinning and reducing compound)

14.3. Transport hazard class(es)

- Classification :



3

14.4. Packing group

III

14.5. Environmental hazards

-

14.6. Special precautions for user

ADR/RID	Class	Code	Pack gr.	Label	Ident.	LQ	Provis.	EQ	Cat.	Tunnel
	3	FI	III	3	30	5 L	163 650 640E	E1	3	D/E

Not subject to this regulation if Q < 450l.

IMDG	Class	2°Label	Pack gr.	LQ	EMS	Provis.	EQ
	3	-	III	5 L	F-E,S-E	163 223 955	E1

Not subject to this regulation if Q < 30l

IATA	Class	2°Label	Pack gr.	Passager	Passager	Cargo	Cargo	note	EQ
	3	-	III	355	60 L	366	220 L	A3 A72	E1
	3	-	III	Y344	10 L	-	-	A3 A72	E1

QUICK DRYING TUNG OIL LIBERON - 526

For limited quantities, see part 2.7 of the OACI/IATA and chapter 3.4 of the ADR and IMDG.

For excepted quantities, see part 2.6 of the OACI/IATA and chapter 3.5 of the ADR and IMDG.

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

No data available.

SECTION 15 : REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

- Classification and labelling information included in section 2:

The following regulations have been used:

- Directive 67/548/EEC and its adaptations
- Directive 1999/45/EC and its adaptations
- Regulation EC 1272/2008 modified by regulation EC 618/2012

- Container information:

No data available.

- Particular provisions :

No data available.

15.2. Chemical safety assessment

No data available.

SECTION 16 : OTHER INFORMATION

Since the user's working conditions are not known by us, the information supplied on this safety data sheet is based on our current level of knowledge and on national and community regulations.

The mixture must not be used for other uses than those specified in section 1 without having first obtained written handling instructions.

It is at all times the responsibility of the user to take all necessary measures to comply with legal requirements and local regulations.

The information in this safety data sheet must be regarded as a description of the safety requirements relating to the mixture and not as a guarantee of the properties thereof.

In compliance with directives 67/548/EEC, 1999/45/EC and their amendments.

Hazard symbols :

Flammable

Contains :

Contains 616-014-00-0 2-BUTANONE OXIME. May produce an allergic reaction.

Risk phrase :

R 10 Flammable.

R 67 Vapours may cause drowsiness and dizziness.

Safety phrase :

S 2 Keep out of the reach of children.

S 46 If swallowed, seek medical advice immediately and show this container or label.

S 51 Use only in well-ventilated areas.

S 29 Do not empty into drains.

Title for H, EUH and R indications mentioned in section 3 :

H226 Flammable liquid and vapour.

H304 May be fatal if swallowed and enters airways.

H312 Harmful in contact with skin.

H317 May cause an allergic skin reaction.

H318 Causes serious eye damage.

H336 May cause drowsiness or dizziness.

H351 Suspected of causing cancer .

EUH066 Repeated exposure may cause skin dryness or cracking.

R 10 Flammable.

R 21 Harmful in contact with skin.

R 40.C3 Limited evidence of a carcinogenic effect.

R 41 Risk of serious damage to eyes.

QUICK DRYING TUNG OIL LIBERON - 526

R 43	May cause sensitisation by skin contact.
R 65	Harmful: may cause lung damage if swallowed.
R 66	Repeated exposure may cause skin dryness or cracking.
R 67	Vapours may cause drowsiness and dizziness.

Abbreviations :

CMR: Carcinogenic, mutagenic or reprotoxic.

ADR : European agreement concerning the international carriage of dangerous goods by Road.

IMDG : International Maritime Dangerous Goods.

IATA : International Air Transport Association.

ICAO : International Civil Aviation Organisation

RID : Regulations concerning the International carriage of Dangerous goods by rail.

WGK : Wassergefahrdungsklasse (Water Hazard Class).

GHS02 : Flame