

Product information

85 51 250 A

Spring Hose Clamp Pliers



- Quick-set adjustment: adjusts by shifting directly onto the workpiece
- Can be used for standard, space-saving, spring wire hose clamps and for spring band clamps up to 70 mm nominal size
- Allows more than 40 mm clamping range
- Rotating, universal grip inserts for reliably gripping the clamps in all positions
- Jaw inserts can also be rotated under load
- Extremely good leverage which allows clamps to be opened easily without great effort
- Slim head design; narrow head width, rotating grip inserts make this an ideal tool, especially in confined areas
- Additional function: detach hoses gently using the serrated jaw
- Chrome vanadium electric steel, forged, oil-hardened



General

Article No.	85 51 250 A
EAN	4003773077329
Pliers	grey atramentized
Handles	with non-slip plastic coating
weight	345 g
Dimensions	250 x 50 x 20 mm
Reach	no
RohS	no

Technical details

Capacity	Ø max. 70 mm
Adjustment positions	25

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000164
ETIM 6.0	EC000164
proficl@ss 6.0	AAA936c004
UNSPSC 13.1	27112112

technical change and errors excepted



