

Product information

97 49 10

- Application: non-insulated tubular cable lugs and crimp terminals in accordance with DIN 46237 and non-insulated butt and crimp connectors in accordance with DIN 46341 0.75 / 1.5 / 2.5 mm²

Crimping dies

For non-insulated tubular cable lugs and crimp terminals and non-insulated butt and crimp connectors in accordance with DIN 46341



General

Article No.	97 49 10
EAN	4003773076896
weight	37 g
Dimensions	12 x 32 mm
Reach	no
RohS	no

Technical details



Applications	non-insulated tubular cable lugs and crimp terminals in accordance with DIN 46237 and non-insulated butt and crimp connectors in accordance with DIN 46341
Capacity in square millimetres	0.25 — 0.75 / 1 — 1.5 / 2.5 mm ²
Number of crimping positions	3
AWG	13 / 15 — 17 / 19 — 20



Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112820

technical change and errors excepted