

Product information

97 49 11

- Application: non-insulated crimp terminals, tube and compression cable lugs in accordance with DIN 46234 and DIN 46235 and non-insulated crimp, butt and press connectors in accordance with DIN 46341 and DIN 46267 4/6/10 mm²

Crimping dies

For non-insulated crimp terminals, tube and compression cable lugs in accordance with DIN 46234 and DIN 46235 and non-insulated crimp, butt and press connectors in accordance with DIN 46341 and DIN 46267



General

Article No.	97 49 11
EAN	4003773076902
weight	37 g
Dimensions	12 x 32 mm
Reach	no
RohS	no

Technical details



Applications	non-insulated crimp terminals, tube and compression cable lugs in accordance with DIN 46234 and DIN 46235 and non-insulated crimp, butt and press connectors in accordance with DIN 46341 and DIN 46267
Capacity in square millimetres	4 / 6 / 10 mm ²
Number of crimping positions	3
AWG	11 / 10 / 7



Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112820

technical change and errors excepted