

## Product information

# 97 78 180

## Crimping Pliers for wire ferrules

IEC 60900 DIN EN 60900




- Light and slim design
- Also as VDE version
- Easy crimping due to optimised transmission ratio
- For crimping wire ferrules according to DIN 46228 parts 1 + 4 from 0.25 to 16 mm<sup>2</sup>
- Crimping in marked half-round dies for reliable connections between the sleeve and the conductor
- 9 particularly deep dies with conical side faces
- Special tool steel, forged, oil-hardened

### General

Article No.	97 78 180
EAN	4003773072003
Head	polished
Handles	insulated with multi-component grips, VDE-tested
weight	254 g
Dimensions	180 x 54 x 28 mm
Standard	DIN EN 60900 IEC 60900
Reach	no
RohS	no

### Technical details



Applications	Wire ferrules
Capacity in square millimetres	0.25 — 16.0 mm <sup>2</sup>
Number of crimping positions	9
AWG	24 — 6

### Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

*technical change and errors excepted*

