

Product information

00 11 01

KNIPEX TwinKey®

For all standard cabinets and shut-off systems

- 10 profiles. 2 crosses. 1 key.
- All common locking systems
- Multifunctional key for the actuation of locking systems from the areas of facilities engineering (heating and sanitation, air conditioning, electro technology), gas and water supply and shut-off-systems
- 8-arm version: two 4-way spider keys connected in a space-saving way using magnets
- Reversible bit: 1,0 x 7 mm slot and PH2 cross slot
- Key and reversible bit joined by stable stainless steel wire
- Weight-optimised zinc die-cast design



General

Article No.	00 11 01
EAN	4003773074670
weight	135 g
Dimensions	92 x 85 x 23 mm
Reach	no
RohS	no

Technical details

Capacity square	5.0 / 6.0 — 7.0 / 8.0 — 9.0 / 10.0 — 11.0 mm
Capacity double-bit key	3 – 5 mm
Capacity half-moon	6 mm
Capacity triangular	7.0 — 8.0 / 9.0 — 10.0 / 11.0 — 12.0 mm

Classification

eCl@ss 5.1.4	21040204
ETIM 5.0	EC000175
ETIM 6.0	EC000175
proficl@ss 6.0	EAC187c008
UNSPSC 13.1	27111707

technical change and errors excepted





