

## Product information

# 00 11 06 V01

## Universal Key "Construction"

For all standard cabinets and shut-off systems

- For locking systems in electrical engineering, the supply of gas and water, air conditioning and ventilation systems, industry, technical installations in buildings, etc.
- 9 different die-cast zinc key-profiles in 1 tool
- With detachable chain and snap hook
- Construction version with plug-in, magnetically held support: catch for locks with profile cylinder hole and male square in steps
- With bit adapter for 1/4" bits with magnet
- Total length: 157 / 95 mm
- Zinc die-casted



General	
Article No.	00 11 06 V01
EAN	4003773075394
weight	255 g
Dimensions	90 x 96 x 20 mm
Reach	no
RohS	no
Technical details	
Capacity square	5.0 / 6.0 / 7.0 — 8.0 / 9.0 — 10.0 mm
Capacity double-bit key	3 – 5 mm
Capacity half-moon	6 mm
Capacity step-like square	6 mm
Capacity triangular	7.0 / 8.0 — 9.0 / 10.0 — 11.0 mm
Classification	
eCl@ss 5.1.4	21040204
ETIM 5.0	EC000175
ETIM 6.0	EC000175
proficl@ss 6.0	EAC187c008
UNSPSC 13.1	27111707

*technical change and errors excepted*

