

Product information

03 06 180

Combination Pliers

DIN ISO 5746 IEC 60900 DIN EN 60900

- With gripping zones for flat and round material, suitable for versatile use
- With cutting edges for soft and hard wire
- Long cutting edges for thicker cables
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 60 HRC
- Special tool steel, forged, multi stage oil-hardened



| General | |
|--|--|
| Article No. | 03 06 180 |
| EAN | 4003773021926 |
| Pliers | chrome plated |
| Head | chrome plated |
| Handles | insulated with multi-component grips, VDE-tested |
| weight | 264 g |
| Dimensions | 180 x 55 x 20 mm |
| Standard | DIN ISO 5746 DIN EN 60900 IEC 60900 |
| Reach | no |
| RohS | no |
| Technical details | |
| Cutting capacities medium hard wire (diameter) | Ø 3.4 mm |
| Cutting capacities hard wire (diameter) | Ø 2.2 mm |
| Cutting capacity copper cable, multiple-stranded | Ø 12.0 mm |
| Cutting capacity copper cable, multiple-stranded | 16.0 mm ² |
| VDE tested | yes |
| Classification | |
| eCl@ss 5.1.4 | 21040301 |
| ETIM 6.0 | EC000836 |
| proficl@ss 6.0 | AAA967c005 |
| UNSPSC 13.1 | 27112139 |

technical change and errors excepted



