

Product information

00 21 20

Tool Case "Vision24" Electric



Well sorted and tidy: the standard tool case with versatile basic equipment

- With 20 brand tools, partly VDE tested according to DIN EN/IEC 60900
- Max. payload: 20 kg
- Volume: 24 litres
- Flexible options due to the individual partitioning of the inserts in the 60 mm deep base tray and its cover plate with six large tool compartments
- Tough ratchet hinges hold the lid open where necessary despite the deadweight of the tools
- Sturdy, ergonomic carrying handle, snaps into place at a 90° angle
- Removable tool board with 15 tool pockets on the base side and six tool pockets as well as a clamp compartment (400 mm wide) on the cover side, held by a push button
- Two lockable steel flip locks protect the case contents from theft
- With circumferential double aluminium frame
- Heavy duty ABS material, black
- Cover and tool boards made from dirt-repellent PP twin-wall sheets
- External dimensions (W x H x D): 480 x 380 x 180 mm; internal dimensions (W x H x D): 460 x 310 x 170 mm

General

Article No.	00 21 20
EAN	4003773052166
weight	6,835 g
Dimensions	176 x 372 mm
Reach	yes
RohS	no





Technical details















Dimension exterior (interior) width mm	480 mm (460 mm)
Dimension exterior (interior) height mm	380 mm (310 mm)
Dimension exterior (interior) depth mm	180 mm (170 mm)

Classification

eCl@ss 5.1.4	21100100
ETIM 5.0	EC000181
ETIM 6.0	EC000181
proficl@ss 6.0	EAA404c076
UNSPSC 13.1	27112117

Content

03 06 180	1 x Combination Pliers 
12 40 200	1 x Self-Adjusting Insulation Stripper (0,03 – 10,0 mm ²) 
16 95 01 SB	1 x KNIPEX ErgoStrip® Universal Stripping Tool (Ø 8,0 – 13,0 mm) 
26 16 200	1 x Snipe Nose Side Cutting Pliers (Stork Beak Pliers) 

Content	
26 26 200	1 x Snipe Nose Side Cutting Pliers (Stork Beak Pliers) 
70 06 160	1 x Diagonal Cutter 
74 06 160	1 x High Leverage Diagonal Cutter 
86 03 180	1 x Pliers Wrench Pliers and a wrench in a single tool 
86 03 180	1 x Pliers Wrench Pliers and a wrench in a single tool 
87 03 250	1 x KNIPEX Cobra® Hightech Water Pump Pliers 
95 16 200	1 x Cable Shears with twin cutting edge (Ø 20 mm / 70 mm ²)
98 20 25	1 x Screwdrivers for slotted screws (2,5 mm) 
98 20 40 SL	1 x Screwdriver (Slim) for slotted screws (4,0 mm) 
98 20 55 SL	1 x Screwdriver (Slim) for slotted screws (5,5 mm) 
98 20 65 SL	1 x Screwdriver (Slim) for slotted screws (6,5 mm) 
98 24 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Phillips® (PH1) 
98 24 02 SL	1 x Screwdriver (Slim) for cross-recessed screws Phillips® (PH2) 
98 25 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ 1) 
98 25 02 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ 2) 
98 52	1 x Cable Knife
005655	1 x Wera Voltage detector, single-pole 247 (0,5 x 3,0 x 70 mm)
Accessories	
00 21 20 LE	Tool Case "Vision24" empty

technical change and errors excepted

Con-Pearl® is a registered trade mark of friedola TECH GmbH