

#### **Product information**

## 00 21 05 LE

### Tool Case "Basic" Empty



#### A classic: everything well sorted

- Two metal flip locks and a three-digit combination lock for secure locking of the cover
- · Label field with two stickers for individual labelling
- Max. payload: 15 kg
- Volume: 27 litres
- Strong, ergonomic handle
- Heavy duty ABS material, black
- Circumferential aluminium frame
- Metal hinges
- · Document compartment in the cover
- Two removable tool boards made of dirt-repellent PP twin-fall sheets with 21 tool pockets
- Base tray, can be fixed by press button, height 50 mm, can be subdivided by inserts; cover plate with 12 large compartments and a flat compartment
- With a total of 41 inserting options



General	
Article No.	00 21 05 LE
EAN	4003773056904
weight	4,500 g
Dimensions	210 x 370 mm
Reach	no
RohS	no

Technical details	
Dimension exterior (interior) width mm	465 mm (440 mm)
Dimension exterior (interior) height mm	200 mm (180 mm)
Dimension exterior (interior) depth mm	410 mm (350 mm)

Classification	
eCl@ss 5.1.4	21100100
ETIM 5.0	EC000181
ETIM 6.0	EC000181
proficl@ss 6.0	EAA404c076
UNSPSC 13.1	27112126

technical change and errors excepted

# **KNIPEX** Quality – Made in Germany







