

## Product information

# 00 21 20 LE

## Tool Case "Vision24"

Empty



- Max. payload: 20 kg
- Volume: 24 litres
- Without tools
- Flexible options due to the individual partitioning of the inserts in the 60 mm deep base tray and its cover plate with six large tool compartments
- Tough ratchet hinges hold the lid open where necessary despite the deadweight of the tools
- Sturdy, ergonomic carrying handle, snaps into place at a 90° angle
- Removable tool board with 15 tool pockets on the base side and six tool pockets as well as a clamp compartment (400 mm wide) on the cover side, held by a push button
- Two lockable steel flip locks protect the case contents from theft
- With circumferential double aluminium frame
- Heavy duty ABS material, black
- Cover and tool boards made from dirt-repellent PP twin-wall sheets
- External dimensions (W x H x D): 480 x 380 x 180 mm; internal dimensions (W x H x D): 460 x 310 x 170 mm

### General

Article No.	00 21 20 LE
EAN	4003773044567
weight	4,485 g
Dimensions	173 x 360 mm
Reach	no
RohS	no

### Technical details

Dimension exterior (interior) width mm	480 mm (460 mm)
Dimension exterior (interior) height mm	175 mm (170 mm)
Dimension exterior (interior) depth mm	370 mm (310 mm)

### Classification

eCl@ss 5.1.4	21100100
ETIM 5.0	EC000181
ETIM 6.0	EC000181
proficl@ss 6.0	EAA404c076
UNSPSC 13.1	27112117

*technical change and errors excepted*

*Con-Pearl® is a registered trade mark of friedola TECH GmbH*