

Product information

11 82 130

Electronics Wire Stripping Shears



- For cutting and stripping solid, multicore and finely stranded conductors with conductor cross-section up to 0.75 mm²
- Pointed head of shears above the wire stripping hole for the accurate cutting of fine wire in confined places
- Easy adjustment to the required diameter of solid or stranded wire with knurled screw and lock nut
- With opening spring
- Special tool steel, oil-hardened

MM

General

Article No.	11 82 130
EAN	4003773071648
Head	polished
Handles	with multi-component grips
weight	85 g
Dimensions	140 x 76 x 18 mm
Reach	yes
RohS	no

Technical details

Stripping capacities in square millimetres	0.01 – 0.75 mm ²
Stripping capacities (diameter)	Ø 0.03 — 1.0 mm

Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000163
ETIM 6.0	EC000163
proficl@ss 6.0	AAA002c003
UNSPSC 13.1	27111506

technical change and errors excepted

