

## Product information

# 87 26 250

## KNIPEX Cobra® VDE Hightech Water Pump Pliers, insulated

DIN ISO 8976 IEC 60900 DIN EN 60900



⚡ 1000 V 



- Adjustment by shifting one jaw directly on to the workpiece: fast, reliable and comfortable handling
- Fine adjustment: allows optimum adjustment to differently sized workpieces and comfortable handle position
- Good access to the workpiece due to slim size of head and joint area
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- Pinch guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened

### General

Article No.	87 26 250
EAN	4003773071495
Pliers	chrome plated
Head	chrome plated
Handles	insulated with multi-component grips, VDE-tested
weight	340 g
Dimensions	250 x 59 x 20 mm
Standard	DIN ISO 8976 DIN EN 60900 IEC 60900
Reach	no
RohS	no

### Technical details

Adjustment positions	24
Capacities for pipes (diameter)	Ø 2 Inch
Capacities for nuts	46 mm
Capacity for pipes, inches (diameter)	Ø 50 mm
VDE tested	yes

### Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000164
ETIM 6.0	EC000164
proficl@ss 6.0	AAA936c004
UNSPSC 13.1	27112112

technical change and errors excepted



Just push the pliers handle to adjust!



Quick setting without using a push-button

