

Product information

90 25 20

Pipe Cutter

For composite pipes and protective tubes

- For cutting composite pipes with diameters from 12.0 to 25.0 mm and for cutting flexible protective tubes with a diameter of 18.0 - 35.0 mm without damaging a potential pipe inside
- A calibration arbor can be fitted, for example for Geberit composite pipes with 11.5 and 15.0 mm dia.
- Blades: special tool steel, oil-hardened, interchangeable
- Tool body: high-grade chrome vanadium electric steel, oil-hardened



WM

General

Article No.	90 25 20
EAN	4003773046004
Pliers	galvanized
Handles	with multi-component grips
weight	332 g
Dimensions	210 x 70 x 20 mm
Reach	yes
RohS	no

Technical details

Cutting capacities protective tubes (diameter)	Ø 18 – 35 mm
--	--------------

Classification

eCl@ss 5.1.4	21040601
ETIM 5.0	EC000148
ETIM 6.0	EC000148
proficl@ss 6.0	AAB927c006
UNSPSC 13.1	23151901

technical change and errors excepted





Clean cut of protective tubes 18 - 35 mm diameter

Composite pipes of 12 - 25 mm dia. are cut cleanly and without deformation