

Product information

94 10 185

Pipe Cutter

For plastic conduit pipes
(electrical installation work)

- For clean cutting of thin-walled plastic pipes (e.g. plastic conduit pipes) with Ø 6.0 - 35.0 mm
- Not suitable for cutting cables
- Blade is replaceable and can be retracted from any position
- Low force requirement due to special blade geometry and optimum transmission
- Minimum operator fatigue due to ergonomic handle design and incremental ratchet blade feed
- Blade: special tool steel, oil-hardened
- Housing: die-cast aluminium, red lacquered



MM

General	
Article No.	94 10 185
EAN	4003773047025
weight	583 g
Dimensions	185 x 190 x 25 mm
Reach	no
RohS	no

Technical details	
Body	die-cast aluminium body, red lacquered
Capacity (diameter)	Ø 6 – 35 mm
Cutting edge length mm	Ø 35 mm

Classification	
eCl@ss 5.1.4	21040601
ETIM 5.0	EC000148
ETIM 6.0	EC000148
proficl@ss 6.0	AAB927c006
UNSPSC 13.1	23151901

technical change and errors excepted



