

## Product information

**95 39 720**

**Movable spare blade for 95 31 720 / 95 32 060**



- For copper and aluminium single conductors as well as multiple stranded cables - also with hard rubber or plastic sheath
- Not suitable for steel wire and wire ropes
- Also suitable for cables with iron sheath reinforcement
- Little hand force required for cutting due to optimum transmission ratio
- High cutting capacity due to two-hand operation and ratchet action
- The blade can be opened in any cutting position
- Handle length with multiple position adjustment from 400 - 610 mm (short transport length, individual adaptation to working conditions)
- Blade: special-quality high-grade tool steel, oil-hardened
- Handles: high-strength oval aluminium tubing

### General

Article No.	95 39 720
EAN	4003773025290
weight	600 g
Dimensions	122 x 5 mm
Reach	no
RohS	no

### Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	AAC484c002
UNSPSC 13.1	27111501

*technical change and errors excepted*