

Product information

97 39 05

Crimping dies

For non-insulated open plug type connectors
(plug width 4.8 + 6.3 mm)

- Just one tool for the most common crimping applications
- Crimping dies changed quickly and easily without any additional tool
- Sorted and protected storage of the interchangeable dies in a round magazine
- Comfortable, powerful crimping pliers in professional quality
- Same reliable crimping results as with fixed crimping dies
- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Chrome vanadium electric steel in special quality, oil-hardened
- Round magazine: plastic, fibreglass-reinforced



General

Article No.	97 39 05
EAN	4003773070078
weight	45 g
Dimensions	32 x 12 mm
Reach	yes
RohS	no

Technical details



Applications	non-insulated open plug type connectors (plug width 4.8 + 6.3 mm)
Capacity in square millimetres	0.5 — 6.0 mm ²
Number of crimping positions	3
AWG	20 — 10

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

technical change and errors excepted