

Product information

97 81 180

Crimping Pliers for wire ferrules

With front loading


- For crimping wire ferrules according to DIN 46228 parts 1 + 4 in the range 0.5 to 6 mm²
- Ideal for work in confined areas, e.g. in narrow and deep switch boxes
- Special tool steel, forged, oil-hardened



General

Article No.	97 81 180
EAN	4003773019794
Head	polished
Handles	plastic coated
weight	209 g
Dimensions	180 x 50 x 13 mm
Reach	no
RohS	no

Technical details



Applications	Wire ferrules
Capacity in square millimetres	0.5 — 6.0 mm ²
Number of crimping positions	1
AWG	20 — 10

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

technical change and errors excepted

