

## Product information

# 97 90 05

## Crimp Assortment

For wire ferrules

- With Crimping Pliers for wire ferrules 97 71 180
- Wire ferrules without collar
- In a TANOS MINI-systainer® (solid plastic box)
- T-Loc fastener for one-handed operation: open or close the systainer® with one turn and connect to a second systainer®
- Opening when connected: fast and simple access to content without disconnecting
- Two stackable plastic inserts with 6 trays each for connectors
- With an assortment of wire ferrules with/without collar




### General

Article No.	97 90 05
EAN	4003773025535
weight	930 g
Dimensions	170 x 68 mm
Reach	no
RohS	no

### Classification

eCl@ss 5.1.4	27400218
ETIM 5.0	EC000524
ETIM 6.0	EC000524
proficl@ss 6.0	EAB559c013
UNSPSC 13.1	27112147

### Content

97 71 180	1 x Crimping Pliers for wire ferrules (0,25 – 16 mm <sup>2</sup> ) 
	50 x Non-insulated wire ferrules 9 mm (150 x 4 mm <sup>2</sup> )
	50 x Non-insulated wire ferrules 30 / 16 mm (200 x 25 mm <sup>2</sup> )
	150 x Non-insulated wire ferrules 6 mm (200 x 0,75 mm <sup>2</sup> )
	150 x Non-insulated wire ferrules 6 mm (200 x 1 mm <sup>2</sup> )
	200 x Non-insulated wire ferrules 7 mm (200 x 1,5 mm <sup>2</sup> )
	200 x Non-insulated wire ferrules 7 mm (200 x 2,5 mm <sup>2</sup> )
	200 x Non-insulated wire ferrules 12 mm (6 mm <sup>2</sup> )
	200 x Non-insulated wire ferrules 12 mm (50 x 10 mm <sup>2</sup> )

## Content

200 x Non-insulated wire ferrules 12 mm (50 x 16 mm <sup>2</sup> )
--

*technical change and errors excepted*

*Systemer® is a registered trademark of TANOS GmbH*

