

Product information

98 07 250

- Parallel smooth gripping jaws
- Variable gripping width
- With scaling for presetting the width apart from the workpiece
- Chrome Vanadium steel

Adjustable Wrench

IEC 60900 DIN EN 60900



⚡ 1000 V   $\angle 22^\circ$

General

Article No.	98 07 250
EAN	4003773071518
Handles	with dipped insulation
weight	590 g
Dimensions	260 x 78 x 32 mm
Standard	DIN EN 60900 IEC 60900
Reach	no
RohS	no

Technical details

Jaw width	8 mm
Head width (W3)	16 mm
Depth	20 mm
Width	2 Inch
Capacities for nuts	34 mm
Capacities for nuts	1 1/8 Inch

Classification

eCl@ss 5.1.4	21040190
ETIM 5.0	EC002192
ETIM 6.0	EC002192
proficl@ss 6.0	AAA789c004
UNSPSC 13.1	27111706

technical change and errors excepted

