

Product information

98 99 13

Tool Roll

15 parts

With insulated tools for works on electrical installations

IEC 60900 DIN EN 60900

- Tool roll made of hard-wearing polyester fabric
- With practical, adjustable quick release fastener
- Equipped with a range of insulated KNIPEX tools for works on electrical installations
- Dimensions, open (L x H): 830 x 310 mm



⚡ 1000V

General

Article No.	98 99 13
EAN	4003773026648
weight	2,660 g
Dimensions	108 x 170 mm
Standard	DIN EN 60900 IEC 60900
Reach	yes
RohS	no

Classification

eCl@ss 5.1.4	21100100
ETIM 5.0	EC000181
ETIM 6.0	EC000181
proficl@ss 6.0	EAA937c005
UNSPSC 13.1	24111507

Content

03 07 200	1 x Combination Pliers 
11 07 160	1 x Insulation Stripper with opening spring, universal (Ø 5,0 mm / 10,0 mm²) 
26 17 200	1 x Snipe Nose Side Cutting Pliers (Stork Beak Pliers) 
70 07 160	1 x Diagonal Cutter 
95 17 200	1 x Cable Shears with twin cutting edge (Ø 20 mm / 70 mm²)
98 00 10	1 x Open-end wrench (10 mm)

Content	
	
98 00 13	1 x Open-end wrench (13 mm) 
98 00 14	1 x Open-end wrench (14 mm) 
98 00 17	1 x Open-end wrench (17 mm) 
98 00 19	1 x Open-end wrench (19 mm) 
98 20 25	1 x Screwdrivers for slotted screws (2,5 mm) 
98 20 40	1 x Screwdrivers for slotted screws (4,0 mm) 
98 20 55	1 x Screwdrivers for slotted screws (5,5 mm) 
98 20 65	1 x Screwdrivers for slotted screws (6,5 mm) 
98 52	1 x Cable Knife
Accessories	
98 99 13 LE	Tool Roll empty 15 pockets

technical change and errors excepted