

Product information

16 40 150

Dismantling Tool

- For dismantling round cables exceeding 25.0 mm dia.
- Removes all sheaths of standard cables
- Suitable for longitudinal and circular cutting
- Cutting depth can be adjusted up to 5.0 mm
- Replaceable blade (both sides can be used)
- Tool body: plastic, fibreglass-reinforced



General

Article No.	16 40 150
EAN	4003773026709
Handles	fibreglass-reinforced polyamide
weight	210 g
Dimensions	150 x 53 x 28 mm
Reach	no
RohS	no

Technical details

Stripping capacities (diameter)	> Ø 25 mm
---------------------------------	-----------

Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000163
ETIM 6.0	EC000163
proficl@ss 6.0	AAA002c003
UNSPSC 13.1	27112104

technical change and errors excepted



Setting the tool for longitudinal cut



Longitudinal cut



Turning the tool for circumferential cut



Circular cut



Adjustable cutting depth