

## Product information

# 00 19 41

### Tool Roll

11 parts

- For telecommunications and electrical engineers
- Tool roll made of hard-wearing polyester fabric
- With practical, adjustable quick release fastener
- Contains eight pliers and three screwdrivers
- Pliers with chrome-plated heads and two-colour dual component handles
- Screwdrivers VDE tested according to DIN EN/IEC 60900 1000V
- Dimensions, open (L x H): 450 x 290 mm










#### General


Article No.	00 19 41
EAN	4003773024729
weight	1,620 g
Dimensions	130 x 60 mm
Reach	yes
RohS	no

#### Classification

eCl@ss 5.1.4	21100100
ETIM 5.0	EC000181
ETIM 6.0	EC000181
proficl@ss 6.0	EAA937c005
UNSPSC 13.1	27112137

#### Content

03 05 160	1 x Combination Pliers 
11 05 160	1 x Insulation Stripper with opening spring, universal (Ø 5,0 mm / 10,0 mm²) 
25 05 160	1 x Snipe Nose Side Cutting Pliers (Radio Pliers) 
30 15 160	1 x Long Nose Pliers 
30 35 160	1 x Long Nose Pliers 
31 15 160	1 x Flat Nose Pliers (Needle-Nose Pliers) 
67 05 140	1 x High Leverage End Cutting Nipper 
70 05 140	1 x Diagonal Cutter

<b>Content</b>	
	
98 20 25	1 x Screwdrivers for slotted screws (2,5 mm) ●
98 20 40	1 x Screwdrivers for slotted screws (4,0 mm) ●
98 24 01	1 x Screwdriver for cross recessed screws Phillips® (PH1) ⊕
<b>Accessories</b>	
00 19 41 LE	Tool Roll empty 11 pockets

*technical change and errors excepted*