

Product information

46 20 A61

Circlip Pliers

For external circlips on shafts

DIN 5254 B



∠90°

- With locking device, can be released
- With replaceable tips made of tempered steel
- Black powder-coated
- DIN 5254 B; 90° angled tips
- Pliers body: rolled steel, high-strength
- Tips: special tool steel, oil-hardened

General

Article No.	46 20 A61
EAN	4003773025030
Pliers	black powder-coated
weight	1,826 g
Dimensions	580 x 151 x 17 mm
Standard	DIN 5254 B
Reach	no
RohS	no

Technical details

Size of shaft	∅ 252 – 400 mm
Style	2
Tips (diameter)	4.5 mm

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC002228
ETIM 6.0	EC002228
proficl@ss 6.0	AAC470c002
UNSPSC 13.1	27112140

technical change and errors excepted