

Product information

95 32 060

Cable Cutter

(ratchet action)

With telescopic handles



- Tool length: 600 - 810 mm
- Weight only approx. 3820 g
- For copper and aluminium single conductors as well as multiple stranded cables - also with hard rubber or plastic sheath
- Not suitable for steel wire, wire ropes and fine-stranded (highly flexible) conductors
- Also suitable for cables with iron sheath reinforcement
- Little hand force required for cutting due to optimum transmission ratio
- High cutting capacity due to two-hand operation and ratchet action
- The blade can be opened in any cutting position
- Handle length with multiple position adjustment from 400 - 610 mm (short transport length, individual adaptation to working conditions)
- Blade: special-quality high-grade tool steel, oil-hardened
- Handles: high-strength oval aluminium tubing

General

Article No.	95 32 060
EAN	4003773071563
Head	burnished
Handles	with multi-component grips
weight	3,820 g
Dimensions	630 x 200 x 60 mm
Reach	yes
RohS	no

Technical details

Cutting capacity copper cable, multiple-stranded	740 mm ²
Cutting capacity copper cable, multiple-stranded	Ø 60 mm
MCM	1,400

Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	AAC484c002
UNSPSC 13.1	23241616

technical change and errors excepted

