

Product information

97 52 65 A

Four-Mandrel Crimping Pliers for turned contacts




- Fine adjustment of pressure depending on the conductor's diameter by means of adjusting wheel
- With table for calculating the settings
- Pliers in a plastic case with foam insert
- For crimping turned contacts
- Four-mandrel crimping for top-quality crimping connections
- Mandrel gauge to check the basic setting
- Repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- Optimum transmission of force due to highly effective lever action for fatigue-reduced operation
- High operation comfort thanks to handy shape
- Chrome vanadium electric steel in special quality, oil-hardened

General

| | |
|-------------|----------------------------|
| Article No. | 97 52 65 A |
| EAN | 4003773071594 |
| Pliers | chrome plated |
| Head | chrome plated |
| Handles | with multi-component grips |
| weight | 604 g |
| Dimensions | 250 x 79 x 42 mm |
| Reach | yes |
| RohS | no |

Technical details



| | |
|--------------------------------|---|
| Applications | turned contacts (Harting; Ilme; Phoenix; Amphenol; Walther; HTS; Contact; Weidmüller) |
| Capacity in square millimetres | 0.14 — 6 mm ² |
| AWG | 26 — 10 |
| Number of crimping positions | 1 |
| Max. contact diameter | 7.5 mm |

Classification

| | |
|----------------|------------|
| eCl@ss 5.1.4 | 21040301 |
| ETIM 5.0 | EC000168 |
| ETIM 6.0 | EC000168 |
| proficl@ss 6.0 | AAA946c003 |
| UNSPSC 13.1 | 27112147 |

Accessories

| | |
|------------|---|
| 97 59 65 2 | Universal Locator for 97 52 65 / 97 52 65 A / 97 52 65 DG / 97 52 65 DG A |
|------------|---|

technical change and errors excepted