



**Quadruple-deck rail-mounted terminal block; Rail-mounted terminal block for electric motor wiring; L1 - L2; with marker carrier**

Item No.: 2002-4141



**Marking**

RoHS ✓  
Compliant

**Business data**

Supplier	WAGO
Item no.	2002-4141
GTIN / EAN	4050821579434
Content	1

**Notes**

**Technical data**


*Miscellaneous*

Ratings per	IEC/EN 60947-7-1
Rated voltage (III / 3) [V]	800 [V]
Rated impulse voltage (III / 3) [kV]	8 [kV]
Rated current [A]	20 [A]

<b>Technical data</b>	
Rated current (2) [A]	25 [A]
Legend (ratings)	(III / 3) Overvoltage category III / Pollution degree 3
Type of wiring	Front-entry wiring
Total number of connection points	4
Total number of potentials	2
Number of levels	4
Connection technology	Push-in CAGE CLAMP®
Number of connection points (connection type)	2
Actuation type	Push-in
Connectable conductor materials	Copper
Nominal cross section	2.5 mm <sup>2</sup>
Solid conductor	0.25 ... 4 mm <sup>2</sup> / 22 ... 12 AWG
Solid conductor, push-in termination	0.75 ... 4 mm <sup>2</sup> / 18 ... 12 AWG
Fine-stranded conductor	0.25 ... 4 mm <sup>2</sup> / 22 ... 12 AWG
Fine-stranded conductor with ferrule, push-in termination, f	0.75 mm <sup>2</sup> / 18 AWG
Strip length	10 ... 12 mm / 0.39 ... 0.47 Inch
Number of connection points (connection type 2)	2
Width	5.2 mm / 0.205 Inch
Height from upper-edge of DIN-35 rail	96.8 mm / 3.811 Inch
Depth	103.5 mm / 4.075 Inch
Type of mounting	Carrier rail 35 x 15
Potential marking	L1 - L2
Color	gray
Insulating material	Polyamide 66 (PA 66)
Fire load [MJ]	0.429 [MJ]
Weight [g]	18.349 [g]
Product Family	TOPJOB® S
Main product function	Multilevel terminal blocks
Product type	Through rail-mount term. blocks

Images & drawings





#### Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.