



2-conductor end terminal block; with fixing flange; for screw or similar mounting types; Fixing hole 3.2 mm Ø

Item No.: 264-307



2-conductor end terminal block; with fixing flange; for screw or similar mounting types; Fixing hole 3.2 mm Ø

Marking

RoHS ✓
Compliant

Business data

| | |
|------------|---------------|
| Supplier | WAGO |
| Item no. | 264-307 |
| GTIN / EAN | 4044918415170 |
| Content | 1 |
| | |
| | |

Notes

Technical data

Miscellaneous

| | |
|---------------------------------|--|
| Connection technology | CAGE CLAMP® |
| Actuation type | Operating tool |
| Connectable conductor materials | Copper |
| Solid conductor | 0.08 ... 2.5 mm ² / 28 ... 12 AWG |
| Fine-stranded conductor | 0.08 ... 2.5 mm ² / 28 ... 12 AWG |
| Strip length | 8 ... 9 mm / 0.31 ... 0.35 Inch |

| Technical data | |
|--|---|
| <i>Total number of connection points</i> | <i>2</i> |
| <i>Total number of potentials</i> | <i>1</i> |
| <i>Number of levels</i> | <i>1</i> |
| <i>Type of wiring</i> | <i>Front-entry wiring</i> |
| <i>Note (conductor cross-section)</i> | <i>12 AWG: THHN, THWN</i> |
| <i>Width</i> | <i>6 mm / 0.236 Inch</i> |
| <i>Height from the surface</i> | <i>22.1 mm / 0.87 Inch</i> |
| <i>Depth</i> | <i>32 mm / 1.26 Inch</i> |
| <i>Design</i> | <i>horizontal</i> |
| <i>Marking level</i> | <i>Center marking</i> |
| <i>Color</i> | <i>green-yellow</i> |
| <i>Fire load [MJ]</i> | <i>0.075 [MJ]</i> |
| <i>Weight [g]</i> | <i>3.864 [g]</i> |
| <i>Packaging type</i> | <i>BOX</i> |
| <i>Main product function</i> | <i>GND cond. term. block</i> |
| <i>Product type</i> | <i>Miniature rail-mount terminal blocks</i> |

Images & drawings





Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.