



4-conductor end terminal block; with fixing flange; for screw or similar mounting types; Fixing hole 3.2 mm Ø

Item No.: 264-337



4-conductor end terminal block; with fixing flange; for screw or similar mounting types; Fixing hole 3.2 mm Ø

Marking

RoHS ✓
Compliant

Business data

Supplier	WAGO
Item no.	264-337
GTIN / EAN	4044918414647
Content	1

Notes

Technical data

Miscellaneous

Legend (ratings)	(III / 3) Overvoltage category III / Pollution degree 3
Connection technology	CAGE CLAMP®
Actuation type	Operating tool
Connectable conductor materials	Copper
Solid conductor	0.08 ... 2.5 mm ² / 28 ... 12 AWG
Fine-stranded conductor	0.08 ... 2.5 mm ² / 28 ... 12 AWG

Technical data	
<i>Strip length</i>	<i>8 ... 9 mm / 0.31 ... 0.35 Inch</i>
<i>Total number of connection points</i>	<i>4</i>
<i>Total number of potentials</i>	<i>1</i>
<i>Number of levels</i>	<i>1</i>
<i>Type of wiring</i>	<i>Front-entry wiring</i>
<i>Note (conductor cross-section)</i>	<i>12 AWG: THHN, THWN</i>
<i>Width</i>	<i>10 mm / 0.394 Inch</i>
<i>Height from the surface</i>	<i>22.1 mm / 0.87 Inch</i>
<i>Depth</i>	<i>32 mm / 1.26 Inch</i>
<i>Design</i>	<i>horizontal</i>
<i>Mounting type</i>	<i>Mounting flange</i>
<i>Marking level</i>	<i>Center marking</i>
<i>Color</i>	<i>green-yellow</i>
<i>Fire load [MJ]</i>	<i>0.108 [MJ]</i>
<i>Weight [g]</i>	<i>6.22 [g]</i>
<i>Packaging type</i>	<i>BOX</i>
<i>Main product function</i>	<i>GND cond. term. block</i>
<i>Product type</i>	<i>Miniature rail-mount terminal blocks</i>

Images & drawings



Printview: 4-conductor end terminal block; with fixing flange; for screw or similar mounting types; Fixing hole 3.2 mm Ø - Item No.: 264-337



Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.