



2-conductor terminal block; with fixing flange; for screw or similar mounting types; Fixing hole 3.2 mm Ø; with 209-123 mounting carrier for DIN 35 rail

Item No.: 261-307



2-conductor terminal block; with fixing flange; for screw or similar mounting types; Fixing hole 3.2 mm Ø; with 209-123 mounting carrier for DIN 35 rail

Marking

RoHS ✓
Compliant

Business data

Supplier	WAGO
Item no.	261-307
GTIN / EAN	4044918611329
Content	1

Notes

Technical data

Miscellaneous


Legend (ratings)	(III / 3) Overtoltage category III / Pollution degree 3
Type of wiring	Side-entry wiring
Total number of connection points	2
Total number of potentials	1

Printview: 2-conductor terminal block; with fixing flange; for screw or similar mounting types; Fixing hole 3.2 mm Ø; with 209-123 mounting carrier for DIN 35 rail - Item No.: 261-307

Technical data	
<i>Number of levels</i>	<i>1</i>
<i>Connection technology</i>	<i>CAGE CLAMP®</i>
<i>Actuation type</i>	<i>Operating tool</i>
<i>Connectable conductor materials</i>	<i>Copper</i>
<i>Solid conductor</i>	<i>0.08 ... 2.5 mm² / 28 ... 14 AWG</i>
<i>Fine-stranded conductor</i>	<i>0.08 ... 2.5 mm² / 28 ... 14 AWG</i>
<i>Strip length</i>	<i>8 ... 9 mm / 0.31 ... 0.35 Inch</i>
<i>Width</i>	<i>6 mm / 0.236 Inch</i>
<i>Height from the surface</i>	<i>18 mm / 0.709 Inch</i>
<i>Depth</i>	<i>28 mm / 1.102 Inch</i>
<i>Design</i>	<i>horizontal</i>
<i>Mounting type</i>	<i>Mounting flange</i>
<i>Marking level</i>	<i>Side marking</i>
<i>Color</i>	<i>green-yellow</i>
<i>Fire load [MJ]</i>	<i>0.042 [MJ]</i>
<i>Weight [g]</i>	<i>2.32 [g]</i>
<i>Main product function</i>	<i>GND cond. term. block</i>
<i>Product type</i>	<i>Miniature rail-mount terminal blocks</i>

Printview: 2-conductor terminal block; with fixing flange; for screw or similar mounting types; Fixing hole 3.2 mm Ø; with 209-123 mounting carrier for DIN 35 rail - Item No.: 261-307

Images & drawings





Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.