



Power tap; for 35 mm² high-current tbs; Module width 8 mm

Item No.: 285-427



Power tap; for 35 mm² high-current tbs; Module width 8 mm

Marking

RoHS ✓
Compliant

Business data

Supplier	WAGO
Item no.	285-427
GTIN / EAN	4045454549626
Content	1

Notes

Technical data

Miscellaneous

Ratings per	IEC/EN 60947-7-1
Rated voltage (III / 3) [V]	800 [V]
Rated impulse voltage (III / 3) [kV]	8 [kV]
Rated current [A]	32 [A]
Connection technology	CAGE CLAMP®
Solid conductor	0.2 ... 6 mm ² / 24 ... 10 AWG

Technical data	
<i>Fine-stranded conductor</i>	<i>0.2 ... 6 mm² / 24 ... 10 AWG</i>
<i>Strip length</i>	<i>12 ... 13 mm / 0.47 ... 0.51 Inch</i>
<i>Total number of connection points</i>	<i>1</i>
<i>Total number of potentials</i>	<i>1</i>
<i>Type of wiring</i>	<i>Side-entry wiring</i>
<i>Width</i>	<i>8 mm / 0.315 Inch</i>
<i>Design</i>	<i>angled</i>
<i>Marking level</i>	<i>Center marking</i>
<i>Color</i>	<i>gray</i>
<i>Fire load [MJ]</i>	<i>0.132 [MJ]</i>
<i>Weight [g]</i>	<i>9.296 [g]</i>
<i>Packaging type</i>	<i>BOX</i>
<i>Product Family</i>	<i>POWER CAGE CLAMP</i>
<i>Main product function</i>	<i>Power tap</i>
<i>Product type</i>	<i>Accessories</i>

Images & drawings





Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.