

## 2.54mm 6A Terminal Blocks

Pitch:

Rated voltage/current:

Operation temperatures:

Withstand voltage: Insulation resistance:

Wire range:


Max. torque value:


2.54mm 150V/6A

-40°C to +105°C 1250V AC for 60s 500MΩ at 500V DC

26 to 18AWG 1.0mm<sup>2</sup>

0.1 Nm







Housing colour: Green

Screw: Zinc-plated steel (A3)
Wire cage: Nickel-plated brass
Pin header: Tin-plated brass
Wire stripping length: 4.5 + 0.5mm

Wire stripping length:  $4.5 \pm 0.5$ mm Wave soldering:  $260^{\circ}$ C for 5s Hand soldering:  $350^{\circ}$ C for 10s





Order code	Poles
21-3900	2
21-3901	3
21-3902	4
21-3903	5
21-3904	6
21-3905	8
21-3906	10
21-3907	12