

5mm 15A Low Profile 45 Degree Terminal Blocks

Pitch: 5mm
 Rated voltage/current: 300V/15A
 Operation temperatures: -40°C to +105°C
 Withstand voltage: 2000V AC for 60s
 Insulation resistance: 500MΩ at 500V DC
 Wire range: 22 to 12AWG 2.5mm²
 Max. torque value: 0.4 Nm



Housing colour: Blue
 Screw: Zinc-plated steel (A3)
 Wire cage: Nickel-plated brass
 Pin header: Tin-plated brass
 Wire stripping length: 6 to 7mm
 Wave soldering: 260°C for 5s
 Hand soldering: 350°C for 10

Order code	Poles
21-3940	2
21-3941	3

