

7.5mm Header Straight Open 15A Terminal Blocks

Specifications



Pitch:	7.5mm
Type:	Vertical, Open-ended
Poles:	2 to 12
Rated Voltage:	300V
Rated Current:	15A
Operational Temperature:	-40°C to +105°C
Withstand Voltage:	2500V AC for 60s
Insulation Resistance:	500MΩ at 500V DC
Wave Soldering:	260°C for 5s
Hand Soldering:	350°C for 10s

Colour and Materials



Housing Colour:	Green
Housing Material:	PA66
Flame Retardancy:	UL94-V0
Pin Header:	Tin-plated brass



Order Code	Poles	Order Code	Poles
21-5410	2	21-5426	8
21-5411	3	21-5427	9
21-5422	4	21-5428	10
21-5423	5	21-5429	11
21-5424	6	21-5430	12
21-5425	7		



Measurements are in mm
unless stated otherwise.



For further information on pricing, delivery, and long-term stock agreements please get in touch with your local business development contact. Telephone our main office on **01206 751166** or email **Sales@Rapidonline.com**.

The information contained in this datasheet is subject to change without notice and replaces all data sheets previously supplied.

