

MFD 25/01/105-01/055

Multiple sealing insert



Product illustrations are exemplary and may differ from the chosen product. Further variants and individual customization, we will gladly provide you on request.



Material	Thermoplastic elastomer
Temp. range min	-40 °C
Temp. range max	100 °C
Protection class	IP66 / IP68
Colour	Black
Ø cable diameter min	5 mm
Ø cable diameter max	10,5 mm
Quantity of cable	2
BxL	20,6 x 11,5 mm
Product Color	RAL 9005
Using for cable gland	SPRINT 25
Order no. RAL 9005	10101255
Type	MFD 25/01/105-01/055
Packing unit	25
ETIM-Classification	EC000441

Remarks:

IP68: Ø cable diameter min. = Ø cable diameter max. - 10%, but not bigger than 1 mm under the Ø cable diameter max.

IP66: for 1 cable 9,5-10,5mm Ø
and 1 cable 4,5-5,5mm Ø

01.03.2018