

ADR 48

Connection thread gasket, EPDM



Product illustrations are exemplary and may differ from the chosen product. Further variants and individual customization, we will gladly provide you on request.



Material	EPDM
Temp. range min	-40 °C
Temp. range max	140 °C
Thread type	PG
Ø Connection thread D	48
Total length TL	3 mm
Product Color	RAL 9005
Order no. RAL 9005	10061428
Type	ADR 48
Packing unit	100
ETIM-Classification	EC000441

19.06.2017